

KOPPELINGEN EN FLEXIBELS / SLANGEN : SNELKOPPELINGEN EXELTOP



- Zelfsluitende snelkoppeling
- EXELTOP cilindermontage
- Geschikt voor industrieel gas
- In messing

Lassen, Snijden, Industriële processen

Toepassingsgebieden

Ontworpen voor implementatie van:

Acetyleen, Zuurstof

Ontworpen voor:

Industriële gassen


Uitgezonderd:

Alle andere gassen

Producten:

Referentie	Korte beschrijving:	Gas	Ingangskoppeling:	Uitgangskoppeling:	Materiaal
197563	KIT EXELTOP QC O2 + BH M16X150 RH	O2	Quick connect-Quick connect F F	M16x1.5 M	
197564	KIT EXELTOP QC C2H2 + BH M16X150 LH	C2H2	Quick connect-Quick connect F F	M16x1.5 LH M	
197565	KIT EXELTOP QC O2 + BH M16X150 + FBA	O2	Quick connect-Quick connect F F	M16x1.5 M	
197566	KIT EXELTOP QC C2H2 + BH M16X150 + FBA	C2H2	Quick connect-Quick connect F F	M16x1.5 LH M	
169944	FEM QUICK CONNECT OX M16X1,5 RH MALE	O2	Quick connect-Quick connect F F	M16x1.5 M	Messing
169947	FEM QUICK CONNECT C2H2 M16X1,5 LH MALE	C2H2	Quick connect-Quick connect F F	M16x1.5 LH M	Messing

Options

	Referentie	Long designation
	197534	Hose clamp ext diameter 13-14MM

Spare parts

Referentie	Referentie wisselstuk	Long designation
197563	197534	Hose clamp ext diameter 13-14MM
	197565	Kit Exeltop Qc O2 + Bh M16X150 + Fba
	197566	Kit Exeltop Qc C2H2 + Bh M16X150 + Fba
197564	197534	Hose clamp ext diameter 13-14MM
197565	197534	Hose clamp ext diameter 13-14MM
197566	197534	Hose clamp ext diameter 13-14MM
169944	197534	Hose clamp ext diameter 13-14MM
169947	197534	Hose clamp ext diameter 13-14MM